


3M™ Nomad™ Aluminum Mat

# The matting that combines aesthetics with excellent dirt trapping functionality.

Choose the new 3M™ Nomad™ Aluminum Mat to give your entrance a new facelift.

## Features of the Mat

- Combine Aesthetic with excellent Scrapping performance.
- Promote Cleaner Environment through 3M™ Nomad™ Dual-Fiber system that scrap, trap and hold soil, dirt and water.
- Customized to fit building entrances with various sizes and shapes.
- Easy to clean and maintain with Flexible Joint system.
- Protected with sound dampening base to reduce impact sound.



Flexible joint




## Carpet Inserts

Recommended to be used with 3M™ Nomad™ Carpet Matting 8850



- Unique dual-fiber design.
- Large crush-resistant polypropylene fibers that scrap, remove and hide loose dirt.
- Small nylon fibers that wick away water from foot and wheeled traffic.

## Standard Colours



Grey

Black



Brown

Burgundy



For door entrance




For door exit



# Specifications for 3M™ Nomad™ Aluminum Mat


## 3M™ Nomad™ Aluminum Mat 2100



Description	Measurement
Matting height (a)	15.0mm
Nomad™ Carpet insert width (b)	25.0mm
Aluminium wall thickness	2.0mm
Aluminium panel width (c)	42.5mm
Space between 2 panels (d)	3.2mm

\* Used with Nomad™ Carpet Mat 8850 insert

## 3M™ Nomad™ Aluminum Mat 2200



Description	Measurement
Matting height (a)	18.0mm
Nomad™ Carpet insert width (b)	50.0mm
Aluminium wall thickness	2.0mm
Aluminium panel width (c)	67.5mm
Space between 2 panels (d)	3.2mm

\* Used with Nomad™ Carpet Mat 8850 insert

3M Singapore  
 3M Commercial Solutions Division  
 1 Yishun Avenue 7  
 Singapore 768923

Tel: 6450 8888  
[www.3Mmatting.sg](http://www.3Mmatting.sg)

